



Temporary Lighting Products, Incandescent Light, Class 1 Div 1, 120V, 100W, 1230 Lumen Output

By Bryant
Catalog # [BRYXI50120V](#)



Temporary Lighting Products, Incandescent Light, Class 1 Div 1,
120V, 100W, 1230 Lumen Output

General

Environmental Conditions	Hazardous Location
Light Output	1230 lm
Light Source	Incandescent
Series	Portable work Light
Type	Incandescent
UPC	781786379800

Electrical Ratings

Wattage	100 W
---------	-------

Conductor Related

Cord Length	50 ft
-------------	-------

Certifications and Compliance

Certification	Class 1, Div 1 Groups C & D
---------------	-----------------------------

Product Assets

[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRYXI50120V-SPEC-EN | REV 7/2023