



Temporary Lighting Products, Incandescent Light, Class 1 Div 1, 12V, 75W, 720 Lumen Output

By Bryant
Catalog # [BRYXI6012V](#)



Temporary Lighting Products, Incandescent Light, Class 1 Div 1,
12V, 75W, 720 Lumen Output

General

Environmental Conditions	Hazardous Location
Light Output	720 lm
Light Source	Incandescent
Series	Portable work Light
Type	Incandescent
UPC	781786379787

Electrical Ratings

Wattage	75 W
---------	------

Conductor Related

Cord Length	60 ft
-------------	-------

Certifications and Compliance

Certification	Class 1, Div 1 Groups C & D
---------------	-----------------------------

Product Assets

[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRYXI6012V-SPEC-EN | REV 7/2023