



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 1/2 Controlled, 15A 125V, 2- Pole 3-Wire Grounding, 5- 15R, White

By Bryant
Catalog # [CBRS15C1WHI](#)

Straight Blade Devices, Receptacles, Duplex, Commercial
Grade, 1/2 Controlled, 15A 125V, 2-Pole 3-Wire Grounding, 5-
15R, White



General

Color	White
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786145924

Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

Electrical Ratings

Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-14 Catalog page](#)
[Catalog Page - Bryant F-13 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-CBRS15C1WHI-SPEC-EN | REV 7/2023