



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, Controlled, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory

By Bryant
Catalog # [CBRS15C2I](#)



Straight Blade Devices, Receptacles, Duplex, Commercial Grade,
Controlled, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory

Features

- Duplex
- Commercial Grade
- Controlled
- 15A 125V
- 2-Pole 3-Wire Grounding

General

Catalog Number	CBRS15C2I
Color	Ivory
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786145962

Dimensions

Display Size	Standard Sized Product
Weight	0.25 lb

Electrical Ratings

Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-14 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - CBRS15C2I](#)