



# Straight Blade Devices, Receptacles, Duplex, Commercial Grade, Controlled, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory

By Bryant  
Catalog # CBR515C2I



Straight Blade Devices, Receptacles, Duplex, Commercial Grade,  
Controlled, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory

## Features

- Duplex
- Commercial Grade
- Controlled
- 15A 125V
- 2-Pole 3-Wire Grounding

## General

Catalog Number	CBRS15C2I
Color	Ivory
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786145962

## Dimensions

Display Size	Standard Sized Product
Weight	0.25 lb

## Electrical Ratings

Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY A-14 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - CBR515C2I](#)