



# Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, 15A 125V, 5-15R

By Bryant  
Catalog # [CBRS15GRYWRTR](#)



Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, Back and Side Wired, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray

## General

Color	Gray
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786146693

## Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

## Electrical Ratings

Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY A-13 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)

