



Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, 15A 125V, 5-15R

By Bryant
Catalog # [CBRS15WWRTR](#)



Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, Back and Side Wired, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

Features

- Commercial Grade
- Back and Side Wired
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

General

Catalog Number	CBRS15WWRTR
Color	White
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786146723

Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

Electrical Ratings

Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-13 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - CBRS15WWRTR](#)