



# Straight Blade Devices, Receptacles, Duplex, Tamper- Resistant Commercial Grade, 20A 125V, 2- Pole 3-Wire Grounding, 5- 20R, Black, Single Pack

By Bryant  
Catalog # [CBRS20BLKTR](#)



Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant Commercial Grade, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Black, Single Pack

## Application

Commercial Specification Grade

## General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786410695

## Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications and Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant A-13 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-CBRS20BLKTR-SPEC-EN | REV 7/2023