



Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, 20A 125V, 5-20R

By Bryant
Catalog # [CBRS20BLKWTR](#)



Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, Back and Side Wired, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black

Features

- Commercial Grade
- Back and Side Wired
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

General

Catalog Number	CBRS20BLKWTR
Color	Black
Number Of Poles	2-Pole
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786146747

Dimensions

Weight	0.2 lb
--------	--------

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY A-13 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - CBRS20BLKWTR](#)