



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 1/2 Controlled, 20A 125V, 2- Pole 3-Wire Grounding, 5- 20R, Ivory

By Bryant
Catalog # CBRS20C11



Straight Blade Devices, Receptacles, Duplex, Commercial Grade,
1/2 Controlled, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Ivory

General

| | |
|-----------------|-------------------|
| Color | Ivory |
| Number Of Poles | 2-Pole |
| Series | Commercial |
| Style | Smooth Face |
| Type | Duplex Receptacle |
| UPC | 781786146143 |

Dimensions

| | |
|--------|---------|
| Weight | 0.25 lb |
|--------|---------|

Electrical Ratings

| | |
|----------------------------|-------|
| Current / Amperage Rating | 20 A |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |

Conductor Related

| | |
|-----------------|--------|
| Number Of Wires | 3-Wire |
|-----------------|--------|

Certifications And Compliance

| | |
|-------------|-------|
| Nema Rating | 5-20R |
|-------------|-------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - BRY A-14 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)