



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, Controlled, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Ivory

By Bryant
Catalog # [CBRS20C2I](#)

Straight Blade Devices, Receptacles, Duplex, Commercial
Grade, Controlled, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,
Ivory



General

Color	Ivory
Number Of Poles	2-Pole
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786146204

Dimensions

Weight	0.25 lb
--------	---------

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-14 Catalog page](#)
[Catalog Page - Bryant F-13 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-CBRS20C2I-SPEC-EN | REV 7/2023