



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, Controlled, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Light White

By Bryant
Catalog # [CBRS20C2WHI](#)



Straight Blade Devices, Receptacles, Duplex, Commercial Grade,
Controlled, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Light
White

Features

- Duplex
- Commercial Grade
- Controlled
- 20A 125V
- 2-Pole 3-Wire Grounding

General

Catalog Number	CBRS20C2WHI
Color	White
Number Of Poles	2-Pole
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786146228

Dimensions

Weight	0.25 lb
--------	---------

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-14 Catalog Page](#)
[Catalog Page - BRY F-13 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - CBRS20C2WHI](#)