



# Straight Blade Devices, Receptacles, Duplex, Tamper- Resistant Commercial Grade, 20A 125V, 2- Pole 3-Wire Grounding, 5- 20R, White, Single Pack

By Bryant  
Catalog # [CBRS20WTR](#)

Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant Commercial Grade, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, White, Single Pack



## Application

Commercial Specification Grade

## General

|                              |   |
|------------------------------|---|
| Color                        | White   |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means |
| Item Type                    | Traditional Duplex Smooth Face                  |
| Material                     | Composite                                       |
| Material - Mounting Hardware | Screw Mounting                                  |
| Number Of Poles              | 2-Pole  |
| OEM Brand Name               | Hubbell Bryant                                  |
| Series                       | Commercial                                      |
| Style                        | Smooth Face                                     |
| Type                         | Duplex Receptacle                               |
| UPC                          | 781786410725                                    |

## Dimensions

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
| Weight       | 0.2 lb                 |

## Electrical Ratings

|                            |                     |
|----------------------------|---------------------|
| Amperage Rating            | 20 A                |
| Connectivity               | Back and Side Wired |
| Current / Amperage Rating  | 20 A                |
| Current Rating             | 20 A                |
| Phase                      | Single Phase        |
| Voltage Rating             | 125 V               |
| Voltage Rating Description | 125 V               |
| Wattage                    | 2500                |

## Conductor Related

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #12 AWG |

## Certifications and Compliance

|             |       |
|-------------|-------|
| Nema Rating | 5-20R |
|-------------|-------|

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalog Page - Bryant A-13 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-CBRS20WTR-SPEC-EN | REV 7/2023