



# Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown, Single Pack

By Bryant  
Catalog # CRS15



Straight Blade Duplex Receptacle, Commercial Grade, 15A 125V,  
2-Pole 3-Wire Grounding, 5-15R

## Features

- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

## Application

Commercial Specification Grade

## General

Catalog Number	CRS15
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786161009

## Dimensions

Dimensions	3.28 in x 1.38 in x 1.07 in
Display Size	Standard Sized Product
Height	1.07 in
Length	3.28 in
Weight	0.2 lb
Width	1.38 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired Only
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R
Standards - RoHS Compliance	CM
Status	

## Logistics

Carton Quantity	10
Pallet Quantity	9000

## Product Assets

[Catalog Page - BRY A-12 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Commercial Grade Receptacles and Switches](#)  
[Literature - General Literature - BRYANT® Wiring Devices](#)  
[Specifications - CRS15](#)