



# Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory, Single Pack

By Bryant  
Catalog # [CRS15ITR](#)



Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Ivory, Single Pack

## Features

- Duplex
- Tamper-Resistant Commercial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5- 15R

## Application

Commercial Specification Grade

## General

Catalog Number	CRS15ITR
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786410787

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Weight	0.15 lb
--------	---------

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired Only
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - BRY A-13 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)
- [Specifications - CRS15ITR](#)