



Straight Blade Devices, Receptacles, Duplex, Tamper- Resistant Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Ivory, Single Pack

By Bryant
Catalog # [CRS20ITR](#)

Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant
Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,
Ivory, Single Pack



Application

Commercial Specification Grade

General

Color	Ivory
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786144057

Dimensions

Display Size	Standard Sized Product
Weight	0.15 lb

Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired Only
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-13 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Tamper-Resistant and Weather
Resistant Receptacles](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-CRS20ITR-SPEC-EN | REV 7/2023