



Locking Devices, Industrial, Male Plug, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Bryant
Catalog # [CS6361](#)

Locking Devices, Industrial, Male Plug, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Heavy Duty Black



Features

- Tough nylon housing offers better impact qualities
- Stainless steel shroud restricts mismatching with the wrong device
- Thermoplastic polyester interior provides heat resistance and impact strength

Application

Extra Heavy Duty Industrial

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Heavy Duty Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Type	Plugs
UPC	781786538139

Dimensions

Dimensions	6.38 in x 2.56 in x 2.56 in
Display Size	Standard Sized
Height	2.56 in
Length	6.38 in
Width	2.56 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-21 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[7716B - Locking Devices, Accessories, Weatherproof Boot, Nylon Plug, For 50A Black](#)
[CS6370A - Locking Devices, Industrial, Receptacle, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)
[CS6360 - Locking Devices, Bryant Wiring Devices, Locking Devices, Industrial, Female Connector Body, 50A 125V, Non-NEMA](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-CS6361-SPEC-EN | REV 7/2023