



Locking Devices, Twist-Lock®, Economy, Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS6369L](#)



Locking Devices, Economy, Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

Application

Industrial Grade

General

Color	Metallic
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Single Armored Heavy Duty Receptacle
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Replacement Part
Style	Heavy Duty
Type	Locking Receptacle
UPC	783585320700

Dimensions

Dimensions	3.30 in x 2.10 in x 2.40 in
Display Size	Standard Sized Product
Height	2.40 in
Length	3.30 in
Width	2.10 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250V AC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Catalog Page - Bryant C-11 Catalog page](#)
[Catalog Page - Bryant H-21 Catalog page](#)
[Catalog Page - Bryant L-10 Catalog page](#)
[Catalog Page - Bryant Q-18 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[SS750 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 50A Twist-Lock® Opening, Standard Size, Stainless Steel](#)
[7383 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Cast Aluminum](#)
[7382 - Wallplates and Boxes, Non-Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Cast Aluminum, Less Flip Lid](#)
[CS6365L - Locking Devices, Twist-Lock®, Economy, Male Plug, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)
[7770 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Cast Aluminum](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-CS6369L-SPEC-EN | REV 7/2023