



Locking Devices, Locking Devices, Industrial, Receptacle, 50A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS8269A](#)



Locking Devices, Industrial, Receptacle, 50A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black

Features

- Thermoset construction offers high heat resistance
- Armored housing provides superior impact resistance
- One piece contacts provide low operating temperatures

General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	CS8269A
Color	Black
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Single Armored Heavy Duty Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Type	Receptacle
UPC	781786253315

Dimensions

Dimensions	3.28 in x 2.12 in x 2.44 in
Display Size	Standard Sized Product
Height	2.44 in
Length	3.28 in
Width	2.12 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250V AC
Wattage	

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY Q-18 Catalog Page](#)
- [Catalog Page - BRY H-21 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-CS8269A-SPEC-EN | REV 6/2024