



Locking Devices, Twist-Lock®, Economy, Female Connector Body, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black



By Bryant
Catalog # [CS8364L](#)

Locking Devices, Economy, Female Connector Body, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

Application

Heavy Duty Industrial

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	783585320731

Dimensions

Dimensions	5.50 in x 2.40 in x 2.40 in
Display Size	Standard
Height	2.40 in
Length	5.50 in
Width	2.40 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current Rating	50 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Conductor Range	#6 AWG
Number Of Conductors	4-Wire Grounding
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Catalog Page - Bryant H-21 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [7716B - Locking Devices, Accessories, Weatherproof Boot, Nylon Plug, For 50A Black](#)
- [7717B - Locking Devices, Accessories, Weatherproof Boot, Nylon Connector Body, For 50A Black](#)
- [CS8375L - Locking Devices, Twist-Lock®, Economy, Flanged Inlet, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black](#)
- [CS8375LC - Locking Devices, Twist-Lock®, Economy, Flanged Inlet, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black](#)
- [CS8365L - Locking Devices, Twist-Lock®, Economy, Male Plug, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)



A proud member of the Hubbell Family.