



Locking Devices, Twist-Lock®, Economy, Receptacle, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS8369L](#)

Economy, Receptacle, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal



Application

Heavy Duty Industrial

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Single Receptacle
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Receptacle
UPC	783585320755

Dimensions

Dimensions	3.30 in x 2.10 in x 2.40 in
Display Size	Standard
Height	2.40 in
Length	3.30 in
Width	2.10 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current Rating	50 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250V AC

Conductor Related

Conductor Range	#6 AWG
Number Of Conductors	4-Wire Grounding
Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Catalog Page - Bryant H-21 Catalog page](#)
[Catalog Page - Bryant Q-18 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[7382 - Wallplates and Boxes, Non-Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Cast Aluminum, Less Flip Lid](#)
[7774CR - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Yellow Polycarbonate](#)
[CS8365L - Locking Devices, Twist-Lock®, Economy, Male Plug, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)
[7383 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Cast Aluminum](#)
[SS750 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 50A Twist-Lock® Opening, Standard Size, Stainless Steel](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-CS8369L-SPEC-EN | REV 7/2023