



Locking Devices, Twist-Lock®, Economy, Flanged Inlet, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS8375LC](#)



Locking Devices, Economy, Flanged Inlet with Cover, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black

General

Application	Extra Heavy Duty Industrial
Catalog Number	CS8375LC
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Male Flanged Inlet
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Style	Heavy Duty
Type	Flanged Inlet
UPC	783585320779

Dimensions

Display Size	Standard Sized Product
Length	2.7 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Phase	Three Phase
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250V AC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-CS8375LC-SPEC-EN | REV 6/2024