



Straight Blade Devices, Receptacles, Duplex, Decorator, Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown, Single Pack

By Bryant
Catalog # DRS15



Straight Blade Devices, Receptacles, Duplex, Decorator, Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown, Single Pack

Features

- Duplex
- Decorator
- Commercial/Industrial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding

Application

Commercial Grade

General

Catalog Number	DRS15
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Decorator
Type	Duplex Receptacle
UPC	781786410466

Dimensions

Dimensions	3.28 in x 1.38 in x 1.07 in
Display Size	Standard Sized Product
Height	1.07 in
Length	3.28 in

Weight	0.15 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-12 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)
[Specifications - DRS15](#)

