



# Straight Blade Devices, Receptacles, Tamper- Resistant Duplex, Decorator, Commercial/Industrial Grade, 15A 125V, 2- Pole 3-Wire Grounding, 5- 15R



By Bryant  
Catalog # [DRS15LATR](#)

Straight Blade Devices, Receptacles, Tamper- Resistant Duplex,  
Decorator, Commercial/Industrial Grade, 15A 125V, 2- Pole 3-  
Wire Grounding, 5-15R, Light Almond, Single Pack

## Features

- Tamper- Resistant Duplex
- Decorator
- Commercial/Industrial Grade
- 15A 125V
- 2- Pole 3-Wire Grounding

## Application

Commercial Grade

## General

Catalog Number	DRS15LATR
Color	Light Almond
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Decorator
Type	Duplex Receptacle
UPC	781786144149

## Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY A-13 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Tamper-Resistant and Weather  
Resistant Receptacles](#)  
[Specifications - DRS15LATR](#)