



# Straight Blade Devices, Receptacles, Duplex, Decorator, Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Black, Single Pack

By Bryant  
Catalog # [DRS20BLK](#)



Straight Blade Devices, Receptacles, Duplex, Decorator,  
Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire  
Grounding, 5-20R, Black, Single Pack

## Application

Commercial Grade

## General

Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Decorator
Type	Duplex Receptacle
UPC	781786410589

## Dimensions

Dimensions	3.28 in x 1.38 in x 1.07 in
Display Size	Standard Sized Product
Height	1.07 in
Length	3.28 in
Weight	0.15 lb
Width	1.38 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
Pallet Quantity	9000

## Product Assets

[Catalog Page - BRY A-12 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Tamper-Resistant and Weather  
Resistant Receptacles](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRY-DRS20BLK-SPEC-EN | REV 5/2024