



# Straight Blade Devices, Commercial Grade, Decorator Duplex, Weather and Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black

By Bryant  
Catalog # DRS20BLKWRTR



Straight Blade Devices, Commercial Grade, Decorator Duplex, Weather and Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black

## General

Application	Commercial Grade
Color	Black
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Item Type	Decorator Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Decorator
Type	Duplex Receptacle
UPC	781786145269

## Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - BRY A-13 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-DRS20BLKWRTR-SPEC-EN | REV 6/2024