



# Straight Blade Devices, Commercial Grade, Decorator Duplex, Weather and Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

By Bryant  
Catalog # [DRS20IWRTTR](#)



Straight Blade Devices, Commercial Grade, Decorator Duplex, Weather and Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

### Features

- Decorator Duplex
- Weather and Tamper Resistant
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

### Application

Commercial Grade

### General

Catalog Number	DRS20IWRTTR
Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Item Type	Decorator Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Decorator
Type	Duplex Receptacle
UPC	781786141667

### Dimensions

Display Size	Standard Sized Product
Weight	0.15 lb

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

### Certifications And Compliance

Nema Rating	5-20R
-------------	-------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - BRY A-13 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)  
[Specifications - DRS20IWRTTR](#)



A Hubbell brand