



# Timer Switches, Single Pole, 8.3A120/277V AC, 30 Minute Delay Time Out, Light Almond

By Bryant

Catalog # [DT5030LA](#)



Timer Switches, Single Pole, 8.3A120/277V AC, 30 Minute Delay Time Out, Light Almond

## Features

- 30 minute timer
- Pre-set 5 button selection with permanent time markings
- Manual override to OFF
- Alert to OFF function - red LED will flash during the final 30 seconds
- Designed for use on 120 or 277V AC circuits

## Performance

- Controls - 5 button selection - Preset time selection
- Controls - LED Indicators - Illuminates once time is selected
- Controls - OFF Switch - 6 seconds to 20 minutes (default set to 10 minutes)
- Electrical - Load Capacity - 120VAC 600W Incandescent, 5A Ballast, 5A CFL/LED 277V, Horsepower rating 1/6
- Environmental - Operating Temperature - 32°F to 122°F (0°C to 50°C) with rate of change not exceeding 20°F(11°C) per hour
- Environmental - Storage - -40°F to 150°F (-40°C to 65°C), 20% to 90% non condensing relative humidity

## General

Catalog Number	DT5030LA
Color	Light Almond
EU RoHS Indicator	No
Humidity	20% to 90% non-condensing relative humidity
Indicator	Illuminates once time is selected
Indicator(s) Type	Red LED
Item Type	Countdown Timer Wall Switch
Material	Polycarbonate
Operating Temperature	32°F to 122°F (0°C to 50°C) with rate of change not exceeding 20°F(11°C) per hour
Series	Fixed Countdown
Specifications	<ul style="list-style-type: none"> <li>• Housing - Polycarbonate</li> <li>• Mounting Bracket - Aluminum</li> <li>• Mounting Strap - Steel</li> </ul>

Storage Temperature Range	-40°F to 150°F (-40°C to 65°C)
Timing Range	OFF, 5, 10, 20, 30 minutes
Type	30 Minutes
UPC	783585256399

## Dimensions

Dimensions	3.81 in x 1.75 in x 2.27 in
Height	2.27 in
Length	3.81 in
Width	1.75 in

## Electrical Ratings

Connectivity	Wire Leads
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277V AC
Wattage	1000/1400 W

## Conductor Related

Wire Length	6 in
Wire Size	#14 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• cULus Listed To UL60730-1 And UL60730-2</li> <li>• Meets ASHRAE 90.1, and CEC Title 24 Compliant</li> </ul>
----------------------	--

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK Z-20 Catalog Page](#)
- [Catalog Page - WDK E-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Residential Catalog](#)
- [Specifications - DT5030LA](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-DT5030LA-SPEC-EN | REV 10/2024