



# Timer Switches, Single Pole, 8.3A120/277V AC, 60 Minute Delay Time Out, Light Almond

By Bryant  
Catalog # [DT5060LA](#)

Timer Switches, Single Pole, 8.3A120/277V AC, 60 Minute  
Delay Time Out, Light Almond



### Features

- 60 minute timer
- Pre-set 5 button selection with permanent time markings
- Manual override to OFF
- Alert to OFF function - red LED will flash during the final 30 seconds
- Designed for use on 120 or 277V AC circuits

### General

Color	<ul style="list-style-type: none"><li>• Light Almond</li><li>• Amande pâle</li></ul>
Humidity	20% to 90% non-condensing relative humidity
Indicator	Illuminates once time is selected
Indicator(s) Type	Red LED
Item Type	Countdown Timer Wall Switch
Material	Polycarbonate
Operating Temperature	32°F to 122°F (0°C to 50°C) with rate of change not exceeding 20°F(11°C) per hour
Performance	<ul style="list-style-type: none"><li>• Controls - 5 button selection - Preset time selection</li><li>• Controls - LED Indicators - Illuminates once time is selected</li><li>• Controls - OFF Switch - 6 seconds to 20 minutes (default set to 10 minutes)</li><li>• Electrical - Load Capacity - 120VAC 600W Incandescent, 5A Ballast, 5A CFL/LED 277V, Horsepower rating 1/6</li><li>• Environmental - Operating Temperature - 32°F to 122°F (0°C to 50°C) with rate of change not exceeding 20°F(11°C) per hour</li><li>• Environmental - Storage - -40°F to 150°F (-40°C to 65°C), 20% to 90% non condensing relative humidity</li></ul>

### Dimensions

Dimensions	3.81 in x 1.75 in x 2.27 in
Height	2.27 in
Length	3.81 in
Width	1.75 in

### Electrical Ratings

Connectivity	Wire Leads
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277V AC
Wattage	1000/1400 W

### Conductor Related

Wire Length	6 in
Wire Size	#14 AWG

### Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• cULus Listed To UL60730-1 And UL60730-2</li><li>• Meets ASHRAE 90.1, and CEC Title 24 Compliant</li></ul>
----------------------	---

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant F-7 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - Residential Catalog](#)

Series	Fixed Countdown
Storage Temperature Range	-40°F to 150°F (-40°C to 65°C)
Timing Range	OFF, 15, 30, 45, 60 minutes
Type	<ul style="list-style-type: none"><li>• 60 Minutes</li><li>• 60 Minutes</li></ul>
UPC	783585256429



A proud member of the Hubbell Family.