



# Liquid-Tight Flexible Metallic Conduit Grip, Connector, 90 Degree Male, 1"

By Bryant  
Catalog # [FC10090](#)



Liquid-Tight Flexible Metallic Conduit Grip, Connector, 90 Degree Male, 1"

## Features

- 90 Degree Male
- 1"

## Application

90 Degree Male

## General

Catalog Number	FC10090
EU RoHS Indicator	No
Material	Steel Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Between Enclosure and Conduit
OEM Brand Name	Hubbell Bryant
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Type	90 Degree With Male Fitting
UPC	781786241268

## Dimensions

Conduit Trade Size 1 in

## Electrical Ratings

Connectivity Cap Nut

## Certifications And Compliance

Nema Rating Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

## Logistics

Carton Quantity 10

## Product Assets

- [Catalog Page - BRY N-25 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Specifications - FC10090](#)