



Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 1 1/4"

By Bryant
Catalog # FC125



Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 1 1/4"

Application

Straight Male

General

Catalog Number	FC125
EU RoHS Indicator	No
Material	Steel Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Between Enclosure and Conduit
OEM Brand Name	Hubbell Bryant
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Type	Straight With Male Fitting
UPC	781786241084

Dimensions

Conduit Trade Size 1 1/4 in

Electrical Ratings

Connectivity Cap Nut

Certifications And Compliance

Nema Rating Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

Logistics

Carton Quantity 2

Product Assets

- [Catalog Page - BRY N-25 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Specifications - FC125](#)