



# Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 1 1/2"

By Bryant  
Catalog # FC150

Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 1 1/2"



## Application

Straight Male

## General

|                              |   |
|------------------------------|---|
| Material                     | Steel Fitting, Stainless Steel Mesh             |
| Material - Mounting Hardware | Between Enclosure and Conduit                   |
| OEM Brand Name               | Hubbell Bryant                                  |
| Series                       | Liquidtight Conduit                             |
| Style                        | For Metal & Non-Metallic PolyTuff I             |
| Temperature Rating           | -40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C) |
| Type                         | Straight With Male Fitting                      |
| UPC                          | 781786241107                                    |

## Dimensions

Conduit Trade Size 1 1/2 in

## Electrical Ratings

Connectivity Cap Nut

## Certifications and Compliance

Nema Rating Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

## Logistics

Carton Quantity 2

## Product Assets

[Catalog Page - Bryant N-25 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Wiring\\_WLFVM032](#)  
[Literature - Wiring\\_WLBVM044](#)  
[Literature - Pulp & Paper Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-FC150-SPEC-EN | REV 7/2023