



Liquid-Tight Flexible Metallic Conduit Grip, Connector, 45 Degree Male, 2 1/2"

By Bryant
Catalog # [FC25090](#)

Liquid-Tight Flexible Metallic Conduit Grip, Connector, 45 Degree Male, 2 1/2"



Application

90 Degree Male

General

Material	Steel Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Between Enclosure and Conduit
OEM Brand Name	Hubbell Bryant
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Type	90 Degree With Male Fitting
UPC	781786241343

Dimensions

Conduit Trade Size 2 1/2 in

Electrical Ratings

Connectivity Cap Nut

Certifications and Compliance

Nema Rating Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

Logistics

Carton Quantity 2

Product Assets

[Catalog Page - Bryant N-25 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-FC25090-SPEC-EN | REV 7/2023