



# Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 3/8"

By Bryant  
Catalog # FC38



Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 3/8"

## Application

Straight Male

## General

Catalog Number	FC38
EU RoHS Indicator	No
Material	Steel Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Between Enclosure and Conduit
OEM Brand Name	Hubbell Bryant
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Type	Straight With Male Fitting
UPC	781786241008

## Dimensions

Conduit Trade Size 3/8 in

## Electrical Ratings

Connectivity Cap Nut

## Certifications And Compliance

Nema Rating Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - BRY N-25 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - FC38](#)