



Liquid-Tight Flexible Metallic Conduit Grip, Connector, 45 Degree Male, 3/8"

By Bryant
Catalog # FC3845

Liquid-Tight Flexible Metallic Conduit Grip, Connector, 45 Degree Male, 3/8"



General

Application	45 Degree Male
Catalog Number	FC3845
EU RoHS Indicator	No
Material	Steel Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Between Enclosure and Conduit
OEM Brand Name	Hubbell Bryant
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Type	45 Degree With Male Fitting
UPC	781786241404

Dimensions

Conduit Trade Size	3/8 in
--------------------	--------

Electrical Ratings

Connectivity	Cap Nut
--------------	---------

Certifications And Compliance

Nema Rating	Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2
-------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY N-25 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand