



Liquid-Tight Flexible Metallic Conduit Grip, Connector, 90 Degree Male, 1/2"

By Bryant
Catalog # FC5090

Liquid-Tight Flexible Metallic Conduit Grip, Connector, 90 Degree Male, 1/2"



General

Application	90 Degree Male
Catalog Number	FC5090
EU RoHS Indicator	No
Material	Steel Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Between Enclosure and Conduit
OEM Brand Name	Hubbell Bryant
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Type	90 Degree With Male Fitting
UPC	781786241220

Dimensions

Conduit Trade Size	1/2 in
--------------------	--------

Electrical Ratings

Connectivity	Cap Nut
--------------	---------

Certifications And Compliance

Nema Rating	Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2
-------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY N-25 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - PULP & PAPER SOLUTIONS](#)



A Hubbell brand