



Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 3/4"

By Bryant
Catalog # [FC75](#)

Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 3/4"



Application

Straight Male

General

Material	Steel Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Between Enclosure and Conduit
OEM Brand Name	Hubbell Bryant
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Type	Straight With Male Fitting
UPC	781786241046

Dimensions

Conduit Trade Size 3/4 in

Electrical Ratings

Connectivity Cap Nut

Certifications and Compliance

Nema Rating Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

Logistics

Carton Quantity 10

Product Assets

- [Catalog Page - Bryant N-25 Catalog page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Wiring_WLFVM032](#)
- [Literature - Wiring_WLBVM044](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - General Literature - BRYANT® Wiring Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-FC75-SPEC-EN | REV 7/2023