



Liquid-Tight Flexible Metallic Conduit Grip, Connector, 45 Degree Male, 3/4"

By Bryant
Catalog # FC7545



Liquid-Tight Flexible Metallic Conduit Grip, Connector, 45 Degree Male, 3/4"

Application

45 Degree Male

General

Catalog Number	FC7545
EU RoHS Indicator	No
Material	Steel Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Between Enclosure and Conduit
OEM Brand Name	Hubbell Bryant
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Type	45 Degree With Male Fitting
UPC	781786241442

Dimensions

Conduit Trade Size 3/4 in

Electrical Ratings

Connectivity Cap Nut

Certifications And Compliance

Nema Rating Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - BRY N-25 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Specifications - FC7545](#)