



Lampholders, Fluorescent Starter, 25W

By Bryant
Catalog # [FS25A](#)

Lampholders, Fluorescent Starter, 25W



Features

25W

Application

Low Wattage Fluorescent

General

Catalog Number	FS25A
Color	White
EU RoHS Indicator	No
Item Type	Fluorescent Starters
Lamp Type	Pre-Heat
Material - Mounting Hardware	Plug-In
Minimum Starting Temperature	40 Degrees F °
OEM Brand Name	Hubbell Bryant
Series	Fluorescent Starters

Start Type	Neo-Start
Type	Neostart
UPC	781786689763

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120/277V AC kV
Wattage	25W

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - BRY O-6 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - FS25A](#)