



## Lampholders, Fluorescent Starter, 4-6-8W

By Bryant  
Catalog # FS5A

Lampholders, Fluorescent Starter, 4-6-8W



### Features

4-6-8W

### Application

Low Wattage Fluorescent

### General

Catalog Number	FS5A
Color	White
EU RoHS Indicator	No
Item Type	Fluorescent Starters
Lamp Type	Pre-Heat
Material - Mounting Hardware	Plug-In
Minimum Starting Temperature	40 Degrees F °
OEM Brand Name	Hubbell Bryant
Series	Fluorescent Starters

Start Type	Neo-Start
Type	Neostart
UPC	781786687943

### Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120/277V AC kV
Wattage	4, 6, 8W

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

[Catalog Page - BRY O-6 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - FS5A](#)



A Hubbell brand