



Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase 120V AC, 400Hz, 3-Pole 4-Wire Grounding, FSL3R, Screw Terminal, Black

By Bryant
Catalog # [FSL3FR](#)

Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase 120V AC, 400Hz, 3-Pole 4-Wire Grounding, NEMA FSL3, Screw Terminal, Black.



Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention
- Designed, tested and approved for use on 400 Hz (400 cycles per second) circuits

Application

Extra Heavy Duty Industrial Specification Grade

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786638280

Dimensions

Dimensions	3.28 in x 1.71 in x 1.14 in
Display Size	Standard Sized Product
Height	1.14 in
Length	3.28 in
Width	1.71 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Single Phase
Voltage Rating	3 Phase Delta 120 V
Voltage Rating Description	3 Phase Delta 120V

Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

Certifications and Compliance

Nema Rating	FSL3-R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant Q-18 Catalog page](#)
[Catalog Page - Bryant H-14 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

7420B - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1) 1.62" Opening, Standard Size, Cast Aluminum
20405 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, For 30A Power Interrupting, Standard Size, Cast Aluminum, New Style
FSL3NP - Locking Devices, Industrial, Male Plug, 30A 3- Phase 120V AC, 400Hz, 3-Pole 4-Wire Grounding, FSL3P, Screw Terminal, Black and White
SS720 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1) 1.60" Opening, Standard Size, Stainless Steel
SB720 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1) 1.60" Opening, Standard Size, Brass



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-FSL3FR-SPEC-EN | REV 7/2023