



Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Wye 120/208V AC 400Hz, 4-Pole 5-Wire Grounding, FSL4R, ScrewTerminal, Black and White

By Bryant
Catalog # FSL4NC



Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Wye 120/208V AC, 400Hz, 4-Pole 5-Wire Grounding, FSL4R, ScrewTerminal, Black and White.

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention
- Designed, tested and approved for use on 400 Hz (400 cycles per second) circuits

Application

Heavy Duty Industrial

General

Catalog Number	FSL4NC
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786638327

Dimensions

Dimensions	2.13 in x 2.13 in x 3.90 in
Display Size	Standard Sized Product
Height	3.9 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	20 A
Voltage Rating	3 Phase Y 120/208 V
Voltage Rating Description	3 Phase Y 120/208 V

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	5-Wire
Number of Conductors	5-Wire Grounding
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	FSL4-R
-------------	--------

Logistics

Carton Quantity	10
Pallet Quantity	2340

Product Assets

[Catalog Page - BRY H-14 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - FSL4NC](#)



A Hubbell brand