



# FSP Adapter Panel, FC/PC (Ceramic Split Sleeve), 6-Port, loaded with 6) Single Mode adapters

By Bryant  
Catalog # FSPFC6

FSP Adapter Panel, FC/PC (Ceramic Split Sleeve), 6-Port, loaded with 6) Single Mode adapters



## Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

## General

Adapter Type	FC Simplex
Application	Interconnect
Catalog Number	FSPFC6
Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) FC Simplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Performance	Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
	Environmental - Operating temperature - 0 °C to +75 °C
Repeatability	0.1 dB SM
Service Life	500 matings
Temperature Rating	-40C to +85C
UPC	662620806679

## Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

## Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.75 dB Max
Return Loss	55

## Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode

## Certifications And Compliance

Industry Standard(s)	TIA-568-C.3
	TIA-604-FOCIS

## Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-FSPFC6-SPEC-EN | REV 6/2024