



Fiber Adapter Panel, JackPack, 6-Port, with 6) F-Connectors

By Bryant
Catalog # [FSPFP6X](#)



Fiber Adapter Panel, JackPack, 6-Port, with 6) F-Connectors

Features

- Includes 6 populated coax connectors

Application

Interconnect

General

EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) Keystone
Material	CRS
Material - Mounting Hardware	Snap-In
Repeatability	0.1 dB
Service Life	500 matings
Style	Adapter Panel
Temperature Rating	0C to 70C
Type	F-Connector
UPC	662620284651

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.75 dB Max
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications and Compliance

Industry Standard(s)	cULus Listed 1863
----------------------	-------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant R-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-FSPFP6X-SPEC-EN | REV 7/2023