



FSP Adapter Panel, Jack, 4-Port, Unloaded

By Bryant
Catalog # [FSPHD4X](#)

FSP Adapter Panel, Jack, 4-Port, Unloaded



Application

Interconnect

Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	JACK_PACK, Unloaded
Catalog Number	FSPHD4X
Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	4) Keystone
Material - Mounting Hardware	Snap-In
Number Of Ports	4
Repeatability	0.1 dB
Service Life	500 matings
Specifications	<ul style="list-style-type: none">• Dimensions - 1.1" W X 5.1" H• Finish - Durable black powder coat• Material - 16ga cold rolled steel

Temperature Rating -40C to +85C
UPC 662620820972

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Return Loss 26

Conductor Related

Fiber Size 125 Micron

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Specifications - FSPHD4X](#)