



# Fiber Optic Panel Adapter, 12-Fiber, 6) LC Duplex, Phosphor Bronze Sleeves, Black

By Bryant  
Catalog # [FSPLCDM6BK](#)

Fiber Optic Panel Adapter, 12-Fiber, 6) LC Duplex, Phosphor Bronze Sleeves, Black



## Features

- Premium Quality and High Performance Design

## Application

Interconnect

## General

|                              |  |
|------------------------------|--|
| Color                        | <ul style="list-style-type: none"><li>• Black</li><li>• Noir</li></ul> |
| EU RoHS Indicator            | No   |
| Enclosure Type               | Various  |
| Environmental Conditions     | Indoor   |
| Item Type                    | 6) LC Duplex   |
| Material                     | Phosphor Bronze  |
| Material - Mounting Hardware | Snap-In  |
| Number Of Ports              | 6  |
| Repeatability                | 0.2 dB   |
| Service Life                 | 500 matings  |
| Single/Multimode             | MM   |
| Temperature Rating           | -40C to +85C   |
| UPC                          | 662620103761   |

## Dimensions

Display Size 5.1" X 1.1"

## Electrical Ratings

Connectivity Receptacle  
Insertion Loss 0.30 dB  
Return Loss 26

## Conductor Related

Fiber Size 125 Micron  
Fiber Type Multimode

## Certifications and Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

## Logistics

Carton Quantity 4

## Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-FSPLCDM6BK-SPEC-EN | REV 7/2023