




Fiber Optic Panel Adapter, 12-Fiber, 6) LC Duplex, Phosphor Bronze Sleeves, Red

By Bryant
Catalog # [FSPLCDM6R](#)

Fiber Optic Panel Adapter, 12-Fiber, 6) LC Duplex, Phosphor Bronze Sleeves, Red



Features

- Premium Quality and High Performance Design

Application

Interconnect

General

Color	Red
EU RoHS Indicator	No
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) LC Duplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Temperature Rating	-40C to +85C
UPC	662620103754

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• TIA-568-C.3• TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	4
-----------------	---

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-FSPLCDM6R-SPEC-EN | REV 7/2023