



Fiber Optic Panel Adapter, 12-Fiber, 6) LC Duplex, Zircon Sleeves, Orange

By Bryant
Catalog # FSPLCDS6OR

Fiber Optic Panel Adapter, 12-Fiber, 6) LC Duplex, Zircon Sleeves, Orange



Features

- Premium Quality and High Performance Design

General

Adapter Type	LC Duplex
Application	Interconnect
Catalog Number	FSPLCDS6OR
Color	Orange
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) LC Duplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.1 dB SM / 0.2 dB MM
Service Life	500 matings
Single/Multimode	SM/MM
Temperature Rating	-40C to +85C
UPC	662620212074

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)	TIA-568-C.3
	TIA-604-FOCIS

Logistics

Carton Quantity	4
-----------------	---

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-FSPLCDS6OR-SPEC-EN | REV 6/2024