



Fiber Adapter Panel, 12-Fiber, 3 LC Quad, Phosphor Bronze, Aqua

By Bryant
Catalog # [FSPLCQM3AQ](#)

Fiber Adapter Panel, 12-Fiber, 3 LC Quad, Phosphor Bronze, Aqua



Features

- Premium Quality and High Performance Design

Application

- Interconnect

General

Adapter Type	LC Quad
Catalog Number	FSPLCQM3AQ
Color	Aqua
EU RoHS Indicator	No
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	3) LC Quad
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Temperature Rating	-40C to +85C
UPC	662620103808

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Insertion Loss 0.30 dB
Return Loss 26

Conductor Related

Fiber Size 125 Micron
Fiber Type Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Specifications - FSPLCQM3AQ](#)