



Fiber Optic Panel Adapter, 12-Fiber, 3) LC Quad, Phosphor Bronze Sleeves, Black

By Bryant
Catalog # [FSPLCQM3BK](#)



Fiber Optic Panel Adapter, 12-Fiber, 3) LC Quad, Phosphor Bronze Sleeves, Black

Features

- Premium Quality and High Performance Design

Application

Interconnect

General

Adapter Type	LC Quad
Catalog Number	FSPLCQM3BK
Color	Black
EU RoHS Indicator	No
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	3) LC Quad
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Temperature Rating	-40C to +85C
UPC	662620103815

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> TIA-568-C.3 TIA-604-FOCIS
----------------------	--

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Specifications - FSPLCQM3BK](#)